



Welcome to the time of

Mini-RIRS


Slim for more

- More safe
- More expelling
- More application

7.5 FR

Flexible Video Ureterorenoscope

HU30S



It provides 39% more irrigation flow per unit time than those common 9.3FR f-URS, which helps to reduce the complications caused by high intrarenal pressure.



HU Series Imaging Part

Digital format with multiple output ports



Specification	
Model	HUV-01
Image output	1024 x 768 pixels
Screen ratio	4:3
Light source control	0-7 grades brightness control
Storage capacity	Maximum 16GB for dynamic or static imaging
Language	Chinese, English, Spanish, Portuguese, French
Power	100-240V~ 50/60HZ
Border type	7 kinds

Ordering information

Product	Item code
Flexible video ureterorenoscope-HU30	
EU Standard (Anti-logic Deflection)	8000B-PA005
US Standard (Logic Deflection)	8000B-PA008
Flexible video ureterorenoscope-HU30S	
EU Standard (Anti-logic Deflection) (L)	8000B-PA011
US Standard (Logic Deflection) (L)	8000B-PA013
EU Standard (Anti-logic Deflection) (R)	8000B-PA012
Imaging Processor	
HUV-01	8002B-PA006

Specifications, design and accessories are subject to change without any notice or obligation on the part of the manufacturer.




Brochure

Flexible Video Ureterorenoscope



“ The fURS has become a mainstay of treatment of nephrolithiasis with increasing indications for surgical modalities.

Takaaki Inoue, corresponding author¹, 2 Shinsuke Okada, 3 Shuzo Hamamoto, and 4 Masato Fujisawa
Retrograde intrarenal surgery: Past, present, and future
PMCID: PMC7940851



We trust in Single-Use Endoscope

Today, single-use ureterorenoscopes are becoming more and more popular among urologists. Since the birth of the first clinically applicable single use ureterorenoscope, numbers of clinical operations have proved its excellent performance no matter on performance or using cost. The single-use ureterorenoscope is becoming one of the main tools in the procedures of urology lithotripsy.

Make f-URS procedures become more
Accessible



Cost-effective

Raise cash flow ratio;
No maintenance cost;
No disinfection cost.



No Cross-infection

Single-use, one scope
for one patient, no cross
infection troubling.



Always Ready To Go

No need to wait for reprocessing,
Always available for
your needs.

Optimized Imaging

160K CMOS sensor chip on tip design;
Optimized algorithm improves 1080P resolution.

User-friendly

Self-Locking bending function;
Smooth bending angle control.

Bullet-tip design

Easier for drilling into ureter;
Reduces the ratio of accidental laser damage on the tip

Toughened Insertion Tube

1:1 torque ratio;
Medical Grade environmentally friendly material.

Intensive Bending

Made by medical grade stainless steel;
Up to 285°up and down bending angle.

Specification

Model	Insertion tube diameter	Working channel diameter	Working Length	Field of View
HU30	9.3FR	3.6FR	650mm	120°
HU30S	7.5FR	3.6FR	650mm	120°

Ergonomic Design

Effectively relieves fatigue

HU30
9.3FR

Substantial for normal cases

HU30S
7.5FR

Superior ultra-slim

1 : 1
Torque Ratio
Never compromising

Environmental

Shaft made by medical grade
environment-friendly materials

Up to 285°

Up & Down deflection
More compensation for more reachable

